

Technical Data

SLF10145-PF Type


SLF10145T-3R3N3R7-PF
SLF10145T-5R6M3R2-PF
SLF10145T-100M2R5-PF
SLF10145T-150M2R2-PF
SLF10145T-220M1R9-PF
SLF10145T-330M1R6-PF
SLF10145T-470M1R4-PF
SLF10145T-680M1R2-PF
SLF10145T-101M1R0-PF
SLF10145T-151MR79-PF
SLF10145T-221MR65-PF
SLF10145T-331MR54-PF
SLF10145T-471MR47-PF
SLF10145T-681MR38-PF
SLF10145T-102MR29-PF
SLF10145T-152MR22-PF

CONTENTS


L-Q Frequency Characteristics
DC Bias & Temperature Characteristics(100kHz)
Temperature Rise
Temperature Characteristics

L-Q Frequency Characteristics

SLF10145T-3R3N3R7-PF




SLF10145T-5R6M3R2-PF




L-Q Frequency Characteristics

SLF10145T-100M2R5-PF




SLF10145T-150M2R2-PF




L-Q Frequency Characteristics

SLF10145T-220M1R9-PF




SLF10145T-330M1R6-PF




L-Q Frequency Characteristics

SLF10145T-470M1R4-PF




SLF10145T-680M1R2-PF




L-Q Frequency Characteristics

SLF10145T-101M1R0-PF




SLF10145T-151MR79-PF




L-Q Frequency Characteristics

SLF10145T-221MR65-PF




SLF10145T-331MR54-PF




L-Q Frequency Characteristics

SLF10145T-471MR47-PF




SLF10145T-681MR38-PF




L-Q Frequency Characteristics

SLF10145T-102MR29-PF




SLF10145T-152MR22-PF




DC Bias & Temperature Characteristics(100kHz)

SLF10145T-3R3N3R7-PF




SLF10145T-5R6M3R2-PF




DC Bias & Temperature Characteristics(100kHz)

SLF10145T-100M2R5-PF




SLF10145T-150M2R2-PF




DC Bias & Temperature Characteristics(100kHz)

SLF10145T-220M1R9-PF




SLF10145T-330M1R6-PF




DC Bias & Temperature Characteristics(100kHz)

SLF10145T-470M1R4-PF




SLF10145T-680M1R2-PF




DC Bias & Temperature Characteristics(100kHz)

SLF10145T-101M1R0-PF




SLF10145T-151MR79-PF




DC Bias & Temperature Characteristics(100kHz)

SLF10145T-221MR65-PF




SLF10145T-331MR54-PF




DC Bias & Temperature Characteristics(100kHz)

SLF10145T-471MR47-PF




SLF10145T-681MR38-PF




DC Bias & Temperature Characteristics(100kHz)

SLF10145T-102MR29-PF




SLF10145T-152MR22-PF




Temperature Rise

SLF10145T-3R3N3R7-PF




SLF10145T-5R6M3R2-PF




Temperature Rise

SLF10145T-100M2R5-PF




SLF10145T-150M2R2-PF




Temperature Rise

SLF10145T-220M1R9-PF




SLF10145T-330M1R6-PF




Temperature Rise

SLF10145T-470M1R4-PF




SLF10145T-680M1R2-PF




Temperature Rise

SLF10145T-101M1R0-PF




SLF10145T-151MR79-PF




Temperature Rise

SLF10145T-221MR65-PF




SLF10145T-331MR54-PF




Temperature Rise

SLF10145T-471MR47-PF




SLF10145T-681MR38-PF




Temperature Rise

SLF10145T-102MR29-PF



SLF10145T-152MR22-PF



Temperature Characteristics

