



# SPECIFICATION

SPEC. No. \_\_\_\_\_

DATE : \_\_\_\_\_

Customer  
\_\_\_\_\_

CUSTOMER'S PRODUCT NAME

TDK PRODUCT NAME  
MULTILAYER CERAMIC CHIP CAPACITORS  
C1005, C1608 Type / 50V to 100V  
C0G Characteristics Tight Tolerance

Please sign and return this specification to your local TDK representatives. If orders are placed without this returned documentation, we must consider you found the specification acceptable.

## THIS SPECIFICATION IS RECEIVED

DATE: \_\_\_\_\_ YEAR \_\_\_\_\_ MONTH \_\_\_\_\_ DAY \_\_\_\_\_

TDK-EPC Corporation  
1-13-1, Nihonbashi, Chuo-ku, Tokyo  
103-0027, Japan

### ENGINEERING

ISSUED	CHECKED	APPROVED
DATE	DATE	DATE

Sales Office \_\_\_\_\_

Sales Tel. \_\_\_\_\_ ( ) \_\_\_\_\_

PRODUCT CLASSIFICATION  
CODE

040320

## 1. SCOPE

This specification is applicable to chip type multilayer ceramic capacitors with a priority over other relevant specifications. Production places defined in this specification shall be TDK-EPC Corporation Japan, TDK (Suzhou) Co., Ltd, TDK-EPC HONG KONG LIMITED, TDK (Malaysia) Sdn. Bhd, and TDK Components U.S.A. Inc.


### EXPLANATORY NOTE:

This specification warrants the quality of the TDK ceramic chip capacitors. The product should be evaluated and confirmed in your product before use. If the use of the product exceeds the bounds of this specification, we can not guarantee its quality and reliability.

## 2. CODE CONSTRUCTION

<u>C1608</u>	<u>C0G</u>	<u>2A</u>	<u>102</u>	<u>G</u>	<u>T</u>
(1)	(2)	(3)	(4)	(5)	(6)

### 1. Type



Type	Typical Dimensions (Unit : mm)				
	L	W	T	B	G
TDK (EIA style)					
C1005 (CC0402)	1.00 ± 0.05	0.50 ± 0.05	0.50 ± 0.05	0.10 min.	0.30 min.
C1608 (CC0603)	1.60 ± 0.10	0.80 ± 0.10	0.80 ± 0.10	0.20 min.	0.30 min.

### 2. Temperature Characteristics (Details are shown in Section 7, No.6)

### 3. Rated Voltage

Symbol	Rated Voltage
2 A	DC 100 V
1 H	DC 50 V

#### 4. Rated Capacitance

Stated in three digits and in units of pico farads (pF).

The first and second digits identify the first and second significant figures of the capacitance; the third digit identifies the multiplier.

R is designated for a decimal point.

Example 220 → 22pF  
 102 → 1,000pF

#### 5. Capacitance tolerance

Symbol	Tolerance
F	± 1 %
G	± 2 %

#### 6. Packaging

Symbol	Packaging
B	Bulk
T	Taping

### 3. RATED CAPACITANCE AND CAPACITANCE TOLERANCE

#### 1. Standard combination of rated capacitance and tolerances

Class	Temperature Characteristics	Capacitance tolerance	Rated capacitance
1	C0G	F (± 1 %) G (± 2 %)	E – 3 series

#### 2. Capacitance Step in E series

E series	Capacitance Step		
E- 3	1.0	2.2	4.7

### 4. OPERATING TEMPERATURE RANGE

T.C.	Min. operating Temperature	Max. operating Temperature	Reference Temperature
C0G	-55°C	125°C	25°C

### 5. STORING CONDITION AND TERM

5 to 40°C at 20 to 70%RH

6 months Max.




### 6. INDUSTRIAL WASTE DISPOSAL

Dispose this product as industrial waste in accordance with the local Industrial Waste Laws.

## 7. PERFORMANCE

No.	Item	Performance	Test or inspection method										
1	External Appearance	No defects which may affect performance.	Inspect with magnifying glass (3X)										
2	Insulation Resistance	10,000MΩ min.	Apply rated voltage for 60s.										
3	Voltage Proof	Withstand test voltage without insulation breakdown or other damage.	<table border="1"> <thead> <tr> <th>Class</th> <th>Apply voltage</th> </tr> </thead> <tbody> <tr> <td>Class1</td> <td>3 × rated voltage</td> </tr> </tbody> </table> <p>Above DC voltage shall be applied for 1 to 5s. Charge / discharge current shall not exceed 50mA.</p>	Class	Apply voltage	Class1	3 × rated voltage						
Class	Apply voltage												
Class1	3 × rated voltage												
4	Capacitance	Within the specified tolerance.	<table border="1"> <thead> <tr> <th>Class</th> <th>Rated Capacitance</th> <th>Measuring frequency</th> <th>Measuring voltage</th> </tr> </thead> <tbody> <tr> <td rowspan="2">Class 1</td> <td>1000pF and under</td> <td>1MHz±10%</td> <td rowspan="2">0.5-5Vrms.</td> </tr> <tr> <td>Over 1000pF</td> <td>1kHz±10%</td> </tr> </tbody> </table>	Class	Rated Capacitance	Measuring frequency	Measuring voltage	Class 1	1000pF and under	1MHz±10%	0.5-5Vrms.	Over 1000pF	1kHz±10%
Class	Rated Capacitance	Measuring frequency	Measuring voltage										
Class 1	1000pF and under	1MHz±10%	0.5-5Vrms.										
	Over 1000pF	1kHz±10%											
5	Q (Class 1)	<table border="1"> <thead> <tr> <th>Rated Capacitance</th> <th>Q</th> </tr> </thead> <tbody> <tr> <td>30pF and over</td> <td>1,000 min.</td> </tr> <tr> <td>Under 30pF</td> <td>400+20×C min.</td> </tr> </tbody> </table> <p>C : Rated capacitance (pF)</p>	Rated Capacitance	Q	30pF and over	1,000 min.	Under 30pF	400+20×C min.	See No.4 in this table for measuring condition.				
Rated Capacitance	Q												
30pF and over	1,000 min.												
Under 30pF	400+20×C min.												
6	Temperature Characteristics of Capacitance (Class 1)	<table border="1"> <thead> <tr> <th>T.C.</th> <th>Temperature Coefficient (ppm/°C)</th> </tr> </thead> <tbody> <tr> <td>C0G</td> <td>0 ± 30</td> </tr> </tbody> </table> <p>Capacitance drift Within ± 0.2% or ±0.05pF, whichever larger.</p>	T.C.	Temperature Coefficient (ppm/°C)	C0G	0 ± 30	<p>Temperature coefficient shall be calculated based on values at 25°C and 85°C temperature.</p> <p>Measuring temperature below 20°C shall be -10°C and -25°C.</p>						
T.C.	Temperature Coefficient (ppm/°C)												
C0G	0 ± 30												

(7. Performed, continued)

No.	Item	Performance	Test or inspection method
7	Robustness of Terminations	No sign of termination coming off, breakage of ceramic, or other abnormal signs.	Reflow solder the capacitor on P.C. board (shown in Appendix 1) and apply a pushing force of 2N (C1005) or 5N (C1608) with 10±1s.  
8	Bending	No mechanical damage.	Reflow solder the capacitors on P.C. board (shown in Appendix 2a or Appendix 2b) and bends 1mm.    (Unit: mm)
9	Solderability	New solder to cover over 75% of termination. 25% may have pin holes or rough spots but not concentrated in one spot. Ceramic surface of "A sections" shall not be exposed due to melting or shifting of termination material.  	Completely soak both terminations in solder at 235±5°C for 2±0.5s.  Solder : H63A (JIS Z 3282)  Flux : Isopropyl alcohol (JIS K 8839) Rosin(JIS K 5902) 25% solid solution.

## (7. Performance, continued)

No.	Item	Performance	Test or inspection method	
10	Resistance to solder heat	External appearance	No cracks are allowed and terminations shall be covered at least 60% with new solder.	
		Capacitance	Characteristics	Change from the value before test
			Class 1	C0G
		Q (Class 1)	Rated Capacitance	Q
			30pF and over	1,000 min.
Under 30pF	$400+20\times C$ min.			
		C : Rated capacitance (pF)		
	Insulation Resistance	Meet the initial spec.		
	Voltage proof	No insulation breakdown or other damage.		
11	Vibration	External appearance	No mechanical damage.	
		Capacitance	Characteristics	Change from the value before test
			Class 1	C0G
Q (Class 1)	Rated Capacitance	Q		
	30pF and over	1,000 min.		
Under 30pF	$400+20\times C$ min.			
		C : Rated capacitance (pF)		
		<p>Completely soak both terminations in solder at <math>260\pm 5^\circ\text{C}</math> for <math>5\pm 1\text{s}</math>.</p> <p>Preheating condition Temp. : <math>150\pm 10^\circ\text{C}</math> Time : 1 to 2min.</p> <p>Flux : Isopropyl alcohol (JIS K 8839) Rosin (JIS K 5902) 25% solid solution.</p> <p>Solder : H63A (JIS Z 3282)</p> <p>Leave the capacitor in ambient conditions for 6 to 24h before measurement.</p>		
		<p>Reflow solder the capacitor on P.C. board (shown in Appendix 1) before testing.</p> <p>Vibrate the capacitor with amplitude of 1.5mm P-P changing the frequencies from 10Hz to 55Hz and back to 10Hz in about 1min.</p> <p>Repeat this for 2h each in 3 perpendicular directions.</p>		


(7. Performance, continued)

No.	Item		Performance	Test or inspection method																				
12	Temperature cycle	External appearance	No mechanical damage.	Reflow solder the capacitor on P.C. board (shown in Appendix 1) before testing.  Expose the capacitor in the conditions step1 through step 4 and repeat 5 times consecutively.  Leave the capacitor in ambient conditions for 6 to 24h (Class 1) or 24±2h (Class 2) before measurement.																				
		Capacitance	<table border="1"> <tr> <td colspan="2">Characteristics</td> <td>Change from the value before test</td> </tr> <tr> <td>Class 1</td> <td>C0G</td> <td>±2.5% or ±0.25pF, whichever larger.</td> </tr> </table>		Characteristics		Change from the value before test	Class 1	C0G	±2.5% or ±0.25pF, whichever larger.														
			Characteristics		Change from the value before test																			
		Class 1	C0G		±2.5% or ±0.25pF, whichever larger.																			
		Q (Class 1)	<table border="1"> <tr> <td>Rated Capacitance</td> <td>Q</td> </tr> <tr> <td>30pF and over</td> <td>1,000 min.</td> </tr> <tr> <td>Under 30pF</td> <td>400+20×C min.</td> </tr> </table> <p style="text-align: center;">C : Rated capacitance (pF)</p>		Rated Capacitance	Q	30pF and over	1,000 min.	Under 30pF	400+20×C min.	<table border="1"> <thead> <tr> <th>Step</th> <th>Temperature(°C)</th> <th>Time (min.)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-55 ±3</td> <td>30 ± 3</td> </tr> <tr> <td>2</td> <td>Reference Temp.</td> <td>2 - 5</td> </tr> <tr> <td>3</td> <td>125 ± 2</td> <td>30 ± 2</td> </tr> <tr> <td>4</td> <td>Reference Temp.</td> <td>2 - 5</td> </tr> </tbody> </table>	Step	Temperature(°C)	Time (min.)	1	-55 ±3	30 ± 3	2	Reference Temp.	2 - 5	3	125 ± 2	30 ± 2	4
Rated Capacitance	Q																							
30pF and over	1,000 min.																							
Under 30pF	400+20×C min.																							
Step	Temperature(°C)	Time (min.)																						
1	-55 ±3	30 ± 3																						
2	Reference Temp.	2 - 5																						
3	125 ± 2	30 ± 2																						
4	Reference Temp.	2 - 5																						
Insulation Resistance	Meet the initial spec.																							
Voltage proof	No insulation breakdown or other damage.																							
13	Moisture Resistance (Steady State)	External appearance	No mechanical damage.	Reflow solder the capacitor on P.C. board (shown in Appendix 1) before testing.  Leave at temperature 40±2°C, 90 to 95%RH for 500 +24,0h.  Leave the capacitor in ambient conditions for 6 to 24h before measurement.																				
		Capacitance	<table border="1"> <tr> <td colspan="2">Characteristics</td> <td>Change from the value before test</td> </tr> <tr> <td>Class 1</td> <td>C0G</td> <td>±5% or ±0.5pF, whichever larger.</td> </tr> </table>		Characteristics		Change from the value before test	Class 1	C0G	±5% or ±0.5pF, whichever larger.														
			Characteristics		Change from the value before test																			
		Class 1	C0G		±5% or ±0.5pF, whichever larger.																			
Q (Class 1)	<table border="1"> <tr> <td>Rated Capacitance</td> <td>Q</td> </tr> <tr> <td>30pF and over</td> <td>350 min.</td> </tr> <tr> <td>10pF and over under 30pF</td> <td>275+5/2×C min.</td> </tr> <tr> <td>Under 10pF</td> <td>200+10×C min.</td> </tr> </table> <p style="text-align: center;">C : Rated capacitance (pF)</p>		Rated Capacitance	Q	30pF and over	350 min.	10pF and over under 30pF	275+5/2×C min.	Under 10pF	200+10×C min.														
	Rated Capacitance	Q																						
	30pF and over	350 min.																						
10pF and over under 30pF	275+5/2×C min.																							
Under 10pF	200+10×C min.																							
Insulation Resistance	1,000MΩ min.																							


(7. Performance, continued)

No.	Item		Performance		Test or inspection method					
14	Moisture Resistance	External appearance	No mechanical damage.		Reflow solder the capacitor on P.C. board (shown in Appendix 1) before testing.  Apply the rated voltage at temperature $40\pm 2^{\circ}\text{C}$ and 90 to 95%RH for 500 +24,0h.  Charge/discharge current shall not exceed 50mA.  Leave the capacitor in ambient conditions for 6 to 24h before measurement.					
		Capacitance	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="2" style="text-align: center;">Characteristics</th> <th style="text-align: center;">Change from the value before test</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">Class 1</td> <td style="text-align: center;">C0G</td> <td style="text-align: center;"><math>\pm 7.5\%</math> or <math>\pm 0.75\text{pF}</math>, whichever larger.</td> </tr> </tbody> </table>			Characteristics		Change from the value before test	Class 1	C0G
	Characteristics		Change from the value before test							
	Class 1	C0G	$\pm 7.5\%$ or $\pm 0.75\text{pF}$ , whichever larger.							
Q (Class 1)	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: center;">Rated Capacitance</th> <th style="text-align: center;">Q</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">30pF and over</td> <td style="text-align: center;">200 min.</td> </tr> <tr> <td style="text-align: center;">Under 30pF</td> <td style="text-align: center;"><math>100+10/3\times C</math> min.</td> </tr> </tbody> </table> <p style="text-align: center; margin-top: 5px;">C : Rated capacitance (pF)</p>		Rated Capacitance	Q	30pF and over	200 min.	Under 30pF	$100+10/3\times C$ min.		
Rated Capacitance	Q									
30pF and over	200 min.									
Under 30pF	$100+10/3\times C$ min.									
Insulation Resistance	500M $\Omega$ min.									
17	Life	External appearance	No mechanical damage.		Reflow solder the capacitor on P.C. board (shown in Appendix 1) before testing.  Below the voltage shall be applied at $125\pm 2^{\circ}\text{C}$ for 1,000 +48, 0h.  Charge/discharge current shall not exceed 50mA.  Leave the capacitor in ambient conditions for 6 to 24h before measurement.					
		Capacitance	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="2" style="text-align: center;">Characteristics</th> <th style="text-align: center;">Change from the value before test</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">Class 1</td> <td style="text-align: center;">C0G</td> <td style="text-align: center;"><math>\pm 3\%</math> or <math>\pm 0.3\text{pF}</math>, whichever larger.</td> </tr> </tbody> </table>			Characteristics		Change from the value before test	Class 1	C0G
	Characteristics		Change from the value before test							
	Class 1	C0G	$\pm 3\%$ or $\pm 0.3\text{pF}$ , whichever larger.							
Q (Class 1)	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: center;">Rated Capacitance</th> <th style="text-align: center;">Q</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">30pF and over</td> <td style="text-align: center;">350 min.</td> </tr> <tr> <td style="text-align: center;">10pF and over under 30pF</td> <td style="text-align: center;"><math>275+5/2\times C</math> min.</td> </tr> <tr> <td style="text-align: center;">Under 10pF</td> <td style="text-align: center;"><math>200+10\times C</math> min.</td> </tr> </tbody> </table> <p style="text-align: center; margin-top: 5px;">C : Rated capacitance (pF)</p>		Rated Capacitance	Q	30pF and over	350 min.	10pF and over under 30pF	$275+5/2\times C$ min.	Under 10pF	$200+10\times C$ min.
Rated Capacitance	Q									
30pF and over	350 min.									
10pF and over under 30pF	$275+5/2\times C$ min.									
Under 10pF	$200+10\times C$ min.									
Insulation Resistance	1,000M $\Omega$ min.									


## Appendix - 1 P.C. Board for reliability test



### Appendix - 2a P.C. Board for bending test Applied for C1005



### Appendix - 2b P.C. Board for bending test Applied for C1608




Material: Glass Epoxy (As per JIS C6484 GE4)

P.C. Board thickness: Appendix-2a      0.8mm  
    Appendix-1, 2b      1.6mm

- Copper (thickness 0.035mm)
- Solder resist

TDK (EIA style)	Dimensions (mm)		
	a	b	c
C1005 (CC0402)	0.4	1.5	0.5
C1608 (CC0603)	1.0	3.0	1.2

## 8. INSIDE STRUCTURE AND MATERIAL


















No.	NAME	MATERIAL
1	Dielectric	CaZrO <sub>3</sub>
2	Electrode	Nickel (Ni)
3	Termination	Copper (Cu)
4		Nickel (Ni)
5		Tin (Sn)

## 9. SOLDERING CONDITION

As for C1005 type, reflow soldering only.



















## 10. Caution

No.	Process	Condition														
1	Operating Condition (Storage, Transportation)	<p>1.1 Storage</p> <ol style="list-style-type: none"> <li>The capacitor must be stored in an ambient temperature of 5 to 40°C with a relative humidity of 20 to 70%RH. The products should be used within 6 months upon receipt.</li> <li>The capacitor must be operated and stored in an environment free of condensation and corrosive gases such as hydrogen sulphide, hydrogen sulphate, chlorine, ammonia and sulfur.</li> <li>Avoid storing in sun light and falling of dew.</li> <li>Do not use capacitor under high humidity and high/low atmospheric pressure which may compromise product reliability.</li> <li>Capacitor should be tested for solderability when stored for long periods of time.</li> </ol> <p>1.2 Handling in transportation</p> <p>In case of the transportation, the performance of the capacitor may be deteriorated depending on the transportation condition. (Refer to JEITA RCR-2335B 9.2 "Handling in transportation")</p>														
2	Circuit design	<p>2.1 Operating temperature</p> <p>Operating temperature should be followed strictly within this specification,</p> <ol style="list-style-type: none"> <li>Do not use capacitors above the maximum allowable operating temperature.</li> <li>Surface temperature including self heating should be below maximum operating temperature. (Due to dielectric loss, capacitors will heat itself when AC is applied. Especially at high frequencies around its SRF, the heat might be so extreme that it may damage itself or the product its mounted on. Please design the circuit so that the maximum temperature of the capacitors (including the self heating) will to be below the maximum allowable operating temperature. Temperature rise at capacitor surface shall be below 20°C)</li> <li>The electrical characteristics of the capacitor will vary depending on the temperature. The capacitor should be selected and designed after taking temperature into consideration.</li> </ol> <p>2.2 Operating voltage</p> <ol style="list-style-type: none"> <li>Operating voltage across the terminals should be below the rated voltage. When AC and DC are super imposed, <math>V_{0-P}</math> must be below the rated voltage. (Reference figures 1 and 2 below). AC or pulse with overshooting, <math>V_{P-P}</math> must be below the rated voltage. (Reference figures 3, 4, and 5 below). When the voltage is started/stopped to the circuit An irregular voltage may be generated for a transit period because of resonance or switching. Be sure to use the capacitors within its rated voltage during this Irregular voltage.</li> </ol> <table border="1" data-bbox="505 1346 1414 1602"> <thead> <tr> <th data-bbox="505 1346 683 1388">Voltage</th> <th data-bbox="683 1346 927 1388">(1) DC voltage</th> <th data-bbox="927 1346 1170 1388">(2) DC+AC voltage</th> <th data-bbox="1170 1346 1414 1388">(3) AC voltage</th> </tr> </thead> <tbody> <tr> <td data-bbox="505 1388 683 1602">Positional Measurement (Rated voltage)</td> <td data-bbox="683 1388 927 1602">  </td> <td data-bbox="927 1388 1170 1602">  </td> <td data-bbox="1170 1388 1414 1602">  </td> </tr> </tbody> </table> <table border="1" data-bbox="505 1629 1414 1879"> <thead> <tr> <th data-bbox="505 1629 683 1671">Voltage</th> <th data-bbox="683 1629 927 1671">(4) Pulse voltage (A)</th> <th data-bbox="927 1629 1170 1671">(5) Pulse voltage (B)</th> </tr> </thead> <tbody> <tr> <td data-bbox="505 1671 683 1879">Positional Measurement (Rated voltage)</td> <td data-bbox="683 1671 927 1879">  </td> <td data-bbox="927 1671 1170 1879">  </td> </tr> </tbody> </table>	Voltage	(1) DC voltage	(2) DC+AC voltage	(3) AC voltage	Positional Measurement (Rated voltage)				Voltage	(4) Pulse voltage (A)	(5) Pulse voltage (B)	Positional Measurement (Rated voltage)		
Voltage	(1) DC voltage	(2) DC+AC voltage	(3) AC voltage													
Positional Measurement (Rated voltage)																
Voltage	(4) Pulse voltage (A)	(5) Pulse voltage (B)														
Positional Measurement (Rated voltage)																

(10. Caution, continued)













No.	Process	Condition																				
2	Circuit design (continued)	<p>2.2 Operating Voltage (continued)</p> <p>2. Even below the rated voltage, if repetitive high AC frequency or pulsed voltage is applied, the reliability of the capacitors may be reduced.</p> <p>3. The effective capacitance will vary depending on applied DC and AC voltages. The capacitor should be selected after considering the voltage affect.</p> <p>2.3 Frequency</p> <p>When Class 2 capacitors are used in AC and/or pulse voltages, the capacitor may self vibrate and generate audible sound (piezoelectric affect).</p>																				
3	Designing P.C. Board	<p>The amount of solder at the terminations has a direct effect on the reliability of the capacitor.</p> <ol style="list-style-type: none"> <li>The greater the amount of solder, the higher the stress on the chip capacitor, and the more likely that it will break. When designing a P.C.board, determine the shape and size of the solder lands to have proper amount of solder on the terminations.</li> <li>Avoid using common solder land for multiple terminations and provide individual solder land for each termination instead.</li> <li>Size and recommended land dimensions provided below:</li> </ol> <div data-bbox="690 787 1356 1060" style="text-align: center;"> <p>The diagram shows a cross-section of a chip capacitor on a PCB. Dimension A is the length of the capacitor body. Dimension B is the length of the solder land on the capacitor side. Dimension C is the height of the solder land. Labels include 'Chip capacitors', 'Solder land', and 'Solder resist'.</p> </div> <table border="1" data-bbox="527 1081 982 1333" style="width: 100%; border-collapse: collapse;"> <caption>Flow soldering (mm)</caption> <thead> <tr> <th>Type</th> <th>C1608 [CC0603]</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.7 - 1.0</td> </tr> <tr> <td>B</td> <td>0.8 - 1.0</td> </tr> <tr> <td>C</td> <td>0.6 - 0.8</td> </tr> </tbody> </table> <table border="1" data-bbox="527 1365 1274 1606" style="width: 100%; border-collapse: collapse;"> <caption>Reflow soldering (mm)</caption> <thead> <tr> <th>Type</th> <th>C1005 [CC0402]</th> <th>C1608 [CC0603]</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.3 - 0.5</td> <td>0.6 - 0.8</td> </tr> <tr> <td>B</td> <td>0.35 - 0.45</td> <td>0.6 - 0.8</td> </tr> <tr> <td>C</td> <td>0.4 - 0.6</td> <td>0.6 - 0.8</td> </tr> </tbody> </table>	Type	C1608 [CC0603]	A	0.7 - 1.0	B	0.8 - 1.0	C	0.6 - 0.8	Type	C1005 [CC0402]	C1608 [CC0603]	A	0.3 - 0.5	0.6 - 0.8	B	0.35 - 0.45	0.6 - 0.8	C	0.4 - 0.6	0.6 - 0.8
Type	C1608 [CC0603]																					
A	0.7 - 1.0																					
B	0.8 - 1.0																					
C	0.6 - 0.8																					
Type	C1005 [CC0402]	C1608 [CC0603]																				
A	0.3 - 0.5	0.6 - 0.8																				
B	0.35 - 0.45	0.6 - 0.8																				
C	0.4 - 0.6	0.6 - 0.8																				

(10. Caution, continued)




No.	Process	Condition												
3	Designing P.C. Board (continued)	<p>4. Recommended chip capacitor layout is provided below:</p> <table border="1"> <thead> <tr> <th data-bbox="506 235 683 310"></th> <th data-bbox="683 235 1040 310">Disadvantage against bending stress</th> <th data-bbox="1040 235 1398 310">Advantage against bending stress</th> </tr> </thead> <tbody> <tr> <td data-bbox="506 310 683 701">Mounting face</td> <td data-bbox="683 310 1040 701"> <p>Perforation or slit</p>  <p>Break P.C. board with mounted side up.</p> </td> <td data-bbox="1040 310 1398 701"> <p>Perforation or slit</p>  <p>Break P.C. board with mounted side down.</p> </td> </tr> <tr> <td data-bbox="506 701 683 1121">Chip arrangement (Direction)</td> <td data-bbox="683 701 1040 1121"> <p>Mount perpendicularly to perforation or slit</p> <p>Perforation or slit</p>  </td> <td data-bbox="1040 701 1398 1121"> <p>Mount in parallel with perforation or slit</p> <p>Perforation or slit</p>  </td> </tr> <tr> <td data-bbox="506 1121 683 1570">Distance from slit</td> <td data-bbox="683 1121 1040 1570"> <p>Closer to slit is higher stress</p>  <p><math>(l_1 &lt; l_2)</math></p> </td> <td data-bbox="1040 1121 1398 1570"> <p>Away from slit is less stress</p>  <p><math>(l_1 &lt; l_2)</math></p> </td> </tr> </tbody> </table>		Disadvantage against bending stress	Advantage against bending stress	Mounting face	<p>Perforation or slit</p>  <p>Break P.C. board with mounted side up.</p>	<p>Perforation or slit</p>  <p>Break P.C. board with mounted side down.</p>	Chip arrangement (Direction)	<p>Mount perpendicularly to perforation or slit</p> <p>Perforation or slit</p> 	<p>Mount in parallel with perforation or slit</p> <p>Perforation or slit</p> 	Distance from slit	<p>Closer to slit is higher stress</p>  <p><math>(l_1 &lt; l_2)</math></p>	<p>Away from slit is less stress</p>  <p><math>(l_1 &lt; l_2)</math></p>
	Disadvantage against bending stress	Advantage against bending stress												
Mounting face	<p>Perforation or slit</p>  <p>Break P.C. board with mounted side up.</p>	<p>Perforation or slit</p>  <p>Break P.C. board with mounted side down.</p>												
Chip arrangement (Direction)	<p>Mount perpendicularly to perforation or slit</p> <p>Perforation or slit</p> 	<p>Mount in parallel with perforation or slit</p> <p>Perforation or slit</p> 												
Distance from slit	<p>Closer to slit is higher stress</p>  <p><math>(l_1 &lt; l_2)</math></p>	<p>Away from slit is less stress</p>  <p><math>(l_1 &lt; l_2)</math></p>												

No.	Process	Condition												
3	Designing P.C. Board (continued)	<p data-bbox="423 165 1349 197">5. Mechanical stress varies according to location of chip capacitor on the P.C.board.</p> <div data-bbox="527 254 1279 772" style="text-align: center;"> </div> <p data-bbox="472 827 1390 884">The relative stress applied to these capacitors during depaneling is in the following order.</p> <p data-bbox="854 884 1057 911" style="text-align: center;"><math>A &gt; B = C &gt; D &gt; E</math></p> <p data-bbox="423 921 732 953">6. Layout recommendation</p> <table border="1" data-bbox="418 963 1448 1822"> <thead> <tr> <th data-bbox="418 963 570 1073">Example</th> <th data-bbox="574 963 857 1073">Use of common solder land</th> <th data-bbox="862 963 1144 1073">Soldering with chassis</th> <th data-bbox="1149 963 1448 1073">Use of common solder land with other SMD</th> </tr> </thead> <tbody> <tr> <td data-bbox="418 1079 570 1430">Need to avoid</td> <td data-bbox="574 1079 857 1430"> </td> <td data-bbox="862 1079 1144 1430"> </td> <td data-bbox="1149 1079 1448 1430"> </td> </tr> <tr> <td data-bbox="418 1436 570 1822">Recommendation</td> <td data-bbox="574 1436 857 1822"> </td> <td data-bbox="862 1436 1144 1822"> <p data-bbox="1024 1724 1097 1755" style="text-align: center;"><math>l^2 &gt; l^1</math></p> </td> <td data-bbox="1149 1436 1448 1822"> </td> </tr> </tbody> </table>	Example	Use of common solder land	Soldering with chassis	Use of common solder land with other SMD	Need to avoid				Recommendation		<p data-bbox="1024 1724 1097 1755" style="text-align: center;"><math>l^2 &gt; l^1</math></p>	
Example	Use of common solder land	Soldering with chassis	Use of common solder land with other SMD											
Need to avoid														
Recommendation		<p data-bbox="1024 1724 1097 1755" style="text-align: center;"><math>l^2 &gt; l^1</math></p>												










(10. Caution, continued)

No.	Process	Condition									
4	Mounting	<p>4.1 Stress from mounting head</p> <p>If the mounting head is adjusted too low, it may induce excessive stress on the chip capacitor and result in cracking. Please take following precautions:</p> <ol style="list-style-type: none"><li>1. Adjust the bottom dead center of the mounting head to reach the P.C. board surface but not contact it.</li><li>2. Adjust the mounting head pressure to be 1 to 3N of static weight.</li><li>3. To minimize the impact energy from mounting head, it is important to provide support from the bottom side of the P.C.board.</li></ol> <p>See following examples.</p> <table border="1" data-bbox="516 562 1403 1087"><thead><tr><th></th><th data-bbox="688 562 1057 611">Not recommended</th><th data-bbox="1057 562 1403 611">Recommended</th></tr></thead><tbody><tr><td data-bbox="516 611 688 842">Single sided mounting</td><td data-bbox="688 611 1057 842"><p>Crack</p></td><td data-bbox="1057 611 1403 842"><p>Support pin</p></td></tr><tr><td data-bbox="516 842 688 1087">Double-sides mounting</td><td data-bbox="688 842 1057 1087"><p>Solder peeling</p><p>Crack</p></td><td data-bbox="1057 842 1403 1087"><p>Support pin</p></td></tr></tbody></table> <p>When the centering jaw is worn, mechanical impact on the capacitor may occur and damage the product. Please control the closing dimension of the centering jaw and provide sufficient preventive maintenance and/or replacement if necessary.</p>		Not recommended	Recommended	Single sided mounting	 <p>Crack</p>	 <p>Support pin</p>	Double-sides mounting	 <p>Solder peeling</p> <p>Crack</p>	 <p>Support pin</p>
	Not recommended	Recommended									
Single sided mounting	 <p>Crack</p>	 <p>Support pin</p>									
Double-sides mounting	 <p>Solder peeling</p> <p>Crack</p>	 <p>Support pin</p>									

(10. Caution, continued)

No.	Process	Condition																			
5	Soldering	<p>5-1. Flux selection</p> <p>Although highly-activated flux gives better solderability, substances which increase activity may also degrade the insulation of the chip capacitor. To avoid such degradation, the following is recommended.</p> <ol style="list-style-type: none"> <li>1. Use a mildly activated rosin flux (less than 0.1wt% chlorine).</li> <li>2. Excessive flux must be avoided. Please provide proper amount of flux.</li> <li>3. When water-soluble flux is used, sufficient washing is necessary.</li> </ol> <p>5. 2 Recommended soldering profile by various methods</p> <div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p><b>Wave soldering</b></p>  </div> <div style="text-align: center;"> <p><b>Reflow soldering</b></p>  </div> </div> <div style="text-align: center; margin-top: 20px;"> <p><b>Manual soldering (Solder iron)</b></p>  </div> <div style="margin-top: 20px;"> <p><b>APPLICATION</b></p> <p>As for C1608 (CC0603) applied to wave soldering and reflow soldering.</p> <p>As for C1005 (CC0402) applied only to reflow soldering.</p> </div> <p>5.3 Recommended soldering peak temp and peak temp duration</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th rowspan="2" style="text-align: center;">Temp./Duration</th> <th colspan="2" style="text-align: center;">Wave soldering</th> <th colspan="2" style="text-align: center;">Reflow soldering</th> </tr> <tr> <th style="text-align: center;">Peak temp(°C)</th> <th style="text-align: center;">Duration(sec.)</th> <th style="text-align: center;">Peak temp(°C)</th> <th style="text-align: center;">Duration(sec.)</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">Sn-Pb Solder</td> <td style="text-align: center;">250 max.</td> <td style="text-align: center;">3 max.</td> <td style="text-align: center;">230 max.</td> <td style="text-align: center;">20 max.</td> </tr> <tr> <td style="text-align: center;">Lead Free Solder</td> <td style="text-align: center;">260 max.</td> <td style="text-align: center;">5 max.</td> <td style="text-align: center;">260 max.</td> <td style="text-align: center;">10 max.</td> </tr> </tbody> </table> <p>Recommended solder compositions</p> <p>Sn-37Pb (Sn-Pb solder)</p> <p>Sn-3.0Ag-0.5Cu (Lead Free Solder)</p>	Temp./Duration	Wave soldering		Reflow soldering		Peak temp(°C)	Duration(sec.)	Peak temp(°C)	Duration(sec.)	Sn-Pb Solder	250 max.	3 max.	230 max.	20 max.	Lead Free Solder	260 max.	5 max.	260 max.	10 max.
Temp./Duration	Wave soldering			Reflow soldering																	
	Peak temp(°C)	Duration(sec.)	Peak temp(°C)	Duration(sec.)																	
Sn-Pb Solder	250 max.	3 max.	230 max.	20 max.																	
Lead Free Solder	260 max.	5 max.	260 max.	10 max.																	








(10. Caution, continued)

No.	Process	Condition																													
5	Soldering (continued)	<p data-bbox="483 178 786 210"><b>5.4 Avoiding thermal shock</b></p> <p data-bbox="483 216 760 247">1. Preheating condition</p> <table border="1" data-bbox="581 247 1398 453"> <thead> <tr> <th data-bbox="581 254 797 296">Soldering</th> <th data-bbox="797 254 1203 296">Type</th> <th data-bbox="1203 254 1398 296">Temp. (°C)</th> </tr> </thead> <tbody> <tr> <td data-bbox="581 306 797 348">Wave soldering</td> <td data-bbox="797 306 1203 348">C1608(CC0603)</td> <td data-bbox="1203 306 1398 348"><math>\Delta T \leq 150</math></td> </tr> <tr> <td data-bbox="581 359 797 401">Reflow soldering</td> <td data-bbox="797 359 1203 401">C1005(CC0402), C1608(CC0603)</td> <td data-bbox="1203 359 1398 401"><math>\Delta T \leq 150</math></td> </tr> <tr> <td data-bbox="581 411 797 453">Manual soldering</td> <td data-bbox="797 411 1203 453">C1005(CC0402), C1608(CC0603)</td> <td data-bbox="1203 411 1398 453"><math>\Delta T \leq 150</math></td> </tr> </tbody> </table> <p data-bbox="483 499 725 531">2. Cooling condition</p> <p data-bbox="532 537 1442 604">Natural cooling using air is recommended. If the chips are dipped into a solvent for cleaning, the temperature difference (<math>\Delta T</math>) must be less than 100°C.</p> <p data-bbox="483 648 714 680"><b>5.5 Amount of solder</b></p> <p data-bbox="532 686 1442 793">Excessive solder will induce higher tensile force on the chip capacitor during temperature changes and may result in chip cracking. Insufficient solder may detach the capacitor from the P.C. board.</p> <div data-bbox="537 821 1414 1230"> <table border="0"> <tr> <td data-bbox="537 821 711 905">Excessive solder</td> <td data-bbox="716 821 1101 926"></td> <td data-bbox="1105 821 1414 905">Higher tensile force on the chip capacitor may cause cracking</td> </tr> <tr> <td data-bbox="537 989 711 1031">Adequate</td> <td data-bbox="716 957 1256 1062"></td> <td></td> </tr> <tr> <td data-bbox="537 1115 711 1199">Insufficient solder</td> <td data-bbox="716 1115 1101 1220"></td> <td data-bbox="1105 1083 1414 1230">Small solder fillet may cause contact failure or not hold the chip capacitor to the P.C. board.</td> </tr> </table> </div> <p data-bbox="483 1268 824 1299"><b>5.6 Solder repair by solder iron</b></p> <p data-bbox="483 1306 889 1337">1. Selection of the soldering iron tip</p> <p data-bbox="532 1344 1393 1514">Tip temperature of solder iron varies by its type, P.C. board material and solder land size. Higher temperatures may provide quicker operation; however, heat shock may cause a crack in the capacitor. Please confirm the tip temperature before soldering and keep the peak temperature and time in accordance with following recommended condition. (Please preheat the chip capacitors with the condition in 5.4 to avoid the thermal shock.)</p> <p data-bbox="553 1545 1365 1577">Recommended solder iron condition (Sn-Pb Solder and Lead Free Solder)</p> <table border="1" data-bbox="581 1577 1360 1675"> <thead> <tr> <th data-bbox="581 1583 776 1625">Temp. (°C)</th> <th data-bbox="776 1583 971 1625">Duration (sec.)</th> <th data-bbox="971 1583 1166 1625">Wattage (W)</th> <th data-bbox="1166 1583 1360 1625">Shape (mm)</th> </tr> </thead> <tbody> <tr> <td data-bbox="581 1635 776 1675">300 max.</td> <td data-bbox="776 1635 971 1675">3 max.</td> <td data-bbox="971 1635 1166 1675">20 max.</td> <td data-bbox="1166 1635 1360 1675">Ø 3.0 max.</td> </tr> </tbody> </table>	Soldering	Type	Temp. (°C)	Wave soldering	C1608(CC0603)	$\Delta T \leq 150$	Reflow soldering	C1005(CC0402), C1608(CC0603)	$\Delta T \leq 150$	Manual soldering	C1005(CC0402), C1608(CC0603)	$\Delta T \leq 150$	Excessive solder		Higher tensile force on the chip capacitor may cause cracking	Adequate			Insufficient solder		Small solder fillet may cause contact failure or not hold the chip capacitor to the P.C. board.	Temp. (°C)	Duration (sec.)	Wattage (W)	Shape (mm)	300 max.	3 max.	20 max.	Ø 3.0 max.
Soldering	Type	Temp. (°C)																													
Wave soldering	C1608(CC0603)	$\Delta T \leq 150$																													
Reflow soldering	C1005(CC0402), C1608(CC0603)	$\Delta T \leq 150$																													
Manual soldering	C1005(CC0402), C1608(CC0603)	$\Delta T \leq 150$																													
Excessive solder		Higher tensile force on the chip capacitor may cause cracking																													
Adequate																															
Insufficient solder		Small solder fillet may cause contact failure or not hold the chip capacitor to the P.C. board.																													
Temp. (°C)	Duration (sec.)	Wattage (W)	Shape (mm)																												
300 max.	3 max.	20 max.	Ø 3.0 max.																												



(10. Caution, continued)

No.	Process	Condition
5	Soldering (continued)	<p>2. Direct contact of the soldering iron with ceramic dielectric of chip the capacitor may cause cracking. Do not touch the ceramic dielectric and the terminations by solder iron.</p> <p>5.7 Sn-Zn solder Sn-Zn solder affects product reliability. Please contact TDK in advance when utilize Sn-Zn solder.</p> <p>5.8 Countermeasure for tombstone The misalignment between the mounted positions of the capacitors and the land patterns should be minimized. The tombstone phenomenon may occur especially when the capacitors are mounted (in longitudinal direction) in the same direction of the reflow soldering. (Refer to JEITA RCR-2335B Annex 1 “Recommendations to prevent the tombstone phenomenon”)</p>
6	Cleaning	<p>1. If an unsuitable cleaning fluid is used, flux residue or some foreign articles may stick to the chip capacitor surface and deteriorate the insulation resistance.</p> <p>2. If cleaning condition is not suitable, it may damage the chip capacitor’s insulation resistance.</p> <p>2.1 Insufficient washing</p> <ol style="list-style-type: none"><li>1. Terminal electrodes may corrode by Halogen in the flux.</li><li>2. Halogen in the flux may adhere on the surface of capacitors, and lower the insulation resistance.</li><li>3. Water soluble flux has higher tendency to have above mentioned problems (1) and (2).</li></ol> <p>2.2 Excessive washing</p> <p>When ultrasonic cleaning is used, excessively high energy output can affect the connection between the ceramic chip capacitor’s body and the terminal electrode. To avoid this, the following is recommended.</p> <p style="text-align: center;">Power: 20 W/ ℓ max. Frequency: 40 kHz max. Washing time: 5 minutes max.</p> <p>2.3 If the cleaning fluid is contaminated, of Halogen concentration can increase, and may bring the same result as insufficient cleaning.</p>

(10. Caution, continued)

No.	Process	Condition						
7	Coating and molding of the P.C. Board	<ol style="list-style-type: none"> <li>When the P.C. board is coated, please verify the quality influence on the product.</li> <li>Please verify carefully that there is no harmful decomposing or reaction gas emission during curing which may damage the chip capacitors.</li> <li>Please verify the curing temperature.</li> </ol>						
8	Handling after chip mounted	<ol style="list-style-type: none"> <li>Please pay attention not to bend or distort the P.C. board after soldering otherwise the chip capacitor may crack.                     <div style="text-align: center; margin: 10px 0;">  </div> </li> <li>When functional check of the P.C. board is performed, higher pin pressure tends to be used for fear of loose contact. But if the pressure is excessive and bend the P.C. board, it may crack the chip capacitor or peel the termination. Please adjust the pins accordingly to ensure the P.C. board is not flexed.                     <table border="1" style="width: 100%; border-collapse: collapse; margin-top: 10px;"> <thead> <tr> <th data-bbox="526 1041 654 1094">Item</th> <th data-bbox="654 1041 1044 1094">Not recommended</th> <th data-bbox="1044 1041 1414 1094">Recommended</th> </tr> </thead> <tbody> <tr> <td data-bbox="526 1094 654 1373" style="text-align: center; vertical-align: middle;">Board bending</td> <td data-bbox="654 1094 1044 1373" style="text-align: center;">  </td> <td data-bbox="1044 1094 1414 1373" style="text-align: center;">  </td> </tr> </tbody> </table> </li> </ol>	Item	Not recommended	Recommended	Board bending		
Item	Not recommended	Recommended						
Board bending								

(10. Caution, continued)

No.	Process	Condition
9	Handling of loose chip capacitors	<p>1. The chip capacitor may crack if dropped, especially large case sizes. Please handle with care and do not use if dropped.</p>  <p>2. When stacking the P.C. board for storage or handling after soldering, the corner of the P.C. board may hit the chip capacitor of a neighboring board and cause a crack.</p> 
10	Capacitance aging	Class 2 capacitors have an aging characteristic, Which is a decrease in capacitance over time due to crystalline changes that occur in ferroelectric ceramics. Careful consideration should be done in case of a time constant circuit.
11	Estimated life and estimated failure rate of capacitors	The estimated life and (failure rate) depend on the temperature and voltage applied. This can be calculated by the equation described in JEITA RCR-2335B Annex 6 "Calculation of the estimated lifetime and the estimated failure rate." The risk can be decreased by reducing the temperature and the voltage but the failure rate can not be guaranteed.
12	Others	<p>The products listed on this specification sheet are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.</p> <p>The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property. Please understand that TDK is not responsible for any damage or liability caused by use of this product in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet:</p> <p>Aerospace/Aviation equipment. Transportation equipment (cars, electric trains, ships, etc.) Medical equipment. Power-generation control equipment. Atomic energy-related equipment. Seabed equipment. Transportation control equipment. Public information-processing equipment. Military equipment. Electric heating apparatus, burning equipment. Disaster prevention/crime prevention equipment. Safety equipment. Other applications that are not considered general-purpose applications.</p> <p>When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc., to ensure higher safety.</p>

## 11. Packaging label

Packaging shall be done to protect the components from the damage during transportation and storing, and a label which has the following information shall be attached.

- 1) Inspection No.
- 2) TDK P/N
- 3) Customer's P/N
- 4) Quantity

\*Composition of Inspection No.

Example    M 0 A - 00 - 000  
                  (a) (b) (c)        (d)        (e)

- a) Line code
- b) Last digit of the year
- c) Month and A for January and B for February and so on. (Skip I)
- d) Inspection Date of the month.
- e) Serial No. of the day

## 12. Bulk packaging quantity

Total number of components in a plastic bag for bulk packaging: 1,000pcs.  
As for C1005 type, not available for bulk packaging.


# 13. TAPE PACKAGING SPECIFICATION

## 1. CONSTRUCTION AND DIMENSION OF TAPING

### 1. Dimensions of carrier tape

Dimensions of paper tape shall be according to Appendix 3, 4.

### 2. Bulk part and leader of taping




### 3. Dimensions of reel

Dimensions of  $\varnothing 178$  reel shall be according to Appendix 5.

Dimensions of  $\varnothing 330$  reel shall be according to Appendix 6.

### 4. Structure of taping




## 2. CHIP QUANTITY

Type	Thickness of chip	Taping Material	Chip quantity (pcs.)	
			$\varnothing 178$ mm reel	$\varnothing 330$ mm reel
C1005	0.50 mm	Paper	10,000	50,000
C1608	0.80 mm	Paper	4,000	10,000

### 3. PERFORMANCE SPECIFICATIONS


1. Peel back cover (top tape)  
0.05-0.7N. (See the following figure.)



2. Carrier tape shall be flexible enough to be wound around a minimum radius of 30mm with components in tape.
3. The missing of components shall be less than 0.1%
4. Components shall not stick to the cover tape.
5. The cover tapes shall not protrude beyond the edges of the carrier tape not shall cover the sprocket holes.

### Appendix 3

#### Paper Tape



(Unit: mm)

Symbol	A	B	C	D	E	F
Type C1005 (CC0402)	( 0.65 )	( 1.15 )	$8.00 \pm 0.30$	$3.50 \pm 0.05$	$1.75 \pm 0.10$	$2.00 \pm 0.05$


  

Symbol	G	H	J	T
Type C1005 (CC0402)	$2.00 \pm 0.05$	$4.00 \pm 0.10$	$\varnothing 1.5 \begin{smallmatrix} +0.10 \\ 0 \end{smallmatrix}$	( 0.60 )

\* The values in the parentheses ( ) are for reference.

### Appendix 4

#### Paper Tape



(Unit: mm)

Symbol	A	B	C	D	E	F
Type C1608 (CC0603)	( 1.10 )	( 1.90 )	$8.00 \pm 0.30$	$3.50 \pm 0.05$	$1.75 \pm 0.10$	$4.00 \pm 0.10$


  

Symbol	G	H	J	T
Type C1608 (CC0603)	$2.00 \pm 0.05$	$4.00 \pm 0.10$	$\varnothing 1.5 \begin{smallmatrix} +0.10 \\ 0 \end{smallmatrix}$	1.10 max.

\* The values in the parentheses ( ) are for reference.

## Appendix 5

(Material: Polystyrene)




(Unit: mm)

Symbol	A	B	C	D	E	W <sub>1</sub>
Dimension	Ø178 ± 2.0	Ø60 ± 2.0	Ø13 ± 0.5	Ø21 ± 0.8	2.0 ± 0.5	9.0 ± 0.3
Symbol	W <sub>2</sub>	r				
Dimension	13.0 ± 1.4	1.0				

## Appendix 6

(Material: Polystyrene)



(Unit: mm)

Symbol	A	B	C	D	E	W
Dimension	Ø382 max. (Nominal Ø330)	Ø50 min.	Ø13 ± 0.5	Ø21 ± 0.8	2.0 ± 0.5	10.0 ± 1.5
Symbol	t	r				
Dimension	2.0 ± 0.5	1.0				

END PAGE